

FEATURES

- Identify signals or voltages easily
- Terminal colours match incoming cables
- Three phase systems are always wired consistently

RS PRO, 800 V Standard Din Rail Terminal

RS Stock No.: 501-803



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

RS Pro standard DIN rail terminal in grey colour, identifies signals or voltages easily. It has a current rating of 32 A and supports wire size of 0.2 to 4 mm². The DIN rail terminal meets UL, NEMKO, GOST and CSA standards.

General Specifications

Colour	Grey	
Number of levels	Single	
Application	Circuit boards and control panels for indus electronics	

Electrical Specifications

Current rating	32A
Voltage rating	800V

Mechanical Specifications

Wire size	0.2mm ² to 4mm ²	
Cable CSA	0.2mm ² to 4mm ²	
Dimensions	48mm x 6mm x 47mm	

Operation Environment Specifications			
Minimum operating temperature	-40°C		
Maximum operating temperature	105°C		



Approvals

Standard met

UL, CSA, NEMKO, GOST







Accessories for RS	501803				
	RS Part				
	No	Description			
End Cover	815688	End Plate for 2.5-10mm Terminals			
Pre Assembly Bar	815795	4mm 10 Way Cross Connectors 27Amps			
Markers	501623	6mm wide blanks for 6mm + terminals			
	501629	6mm wide numbered 1-50 markers			
	501679	6mm numbered 51-100 markers			
Also available in	815666	2.5-4mm Terminal Beige			
	815672	2.5-4mm terminal Blue			
	501720	4mm din rail terminal brown			
	501645	4mm din rail terminal black			
	501803	4mm din rail terminal grey			
	501932	4mm din rail terminal white			
	501651	4mm din rail terminal orange			
	501663	4mm din rail terminal yellow			
	501673	4mm din rail terminal red			