


PRODUCT DATA SHEET H15R Core





2 - PRODUCT DATA SHEET V211110

H15R Core

PRODUCT DESCRIPTION

The H15R Core combines outstanding luminosity and clickless focusability. Long runtimes are guaranteed thanks to its powerful, removable battery with practical Magnetic Charging System. The Wheel Switch on the lamp head makes for easy operation and brightness control, while the lamp head itself rotates seamlessly so you can quickly direct light to where you need it most. And it is well protected from dust and water, making the H15R Core a perfect choice for demanding users.

- Extremely powerful headlamp with our patented³ Advanced Focus System
- Intuitive operation and stepless dimming with the Wheel Switch
- 120 degrees of lamp head rotation
- Flex Sealing Technology provides superior protection against dust and water (IP67)
- · Ledlenser Connecting System: new standardized interface that offers connection to various accessories

| TECHNICAL DATA | |
|------------------------------|------------------------|
| Head diameter [mm] | 47 |
| Weight incl. batteries [g] | 380 |
| Weight without batteries [g] | 230 |
| Focus function | Yes |
| Head material | PC |
| Tube material | Aluminum alloy |
| Optic | Plastic lense (PMMA) |
| Headband material | Elastic fabric |
| Headband type | Side overhead headband |
| Head movement type | Stepless movement |
| Head movement angle [°] | 120 |
| Headband specifications | Detachable, |
| | Elastic, |
| | Washable |

| POWER SUPPLY | |
|--|----------------------|
| Power source type | Rechargeable battery |
| Battery quantity | 1 |
| Battery type | Li-ion |
| Battery replaceable | Yes |
| Total battery voltage [V] | 7.4 |
| Total battery capacity [mAh] | 4800 |
| Total battery energy ² [Wh] | 35.52 |
| Rechargeable | Yes |
| Charging time ⁵ [min] | 330 |
| Energy modes | Constant Light |
| Energy status indicator | Battery Indicator, |
| | Charge Indicator, |
| | Low Battery Warning |

| FURTHER SPECIFICATIONS | | |
|--------------------------------|------------|--|
| IP class | IP67 | |
| Drop test (drop height) [m] | 1.5 | |
| Working temperature range [°C] | -20 to +40 | |

LIGHT FUNCTIONS

Boost, Power, Low Power

| LIGHT SOURCE | |
|-----------------------------|--------------|
| Amount LEDs | 1 |
| LED type | Xtreme LED |
| Color | White |
| Color temperature [K] | 6000 to 7500 |
| Color rendering index (CRI) | 70 |

| LIGHT VALUES | 5 | | |
|--------------------------------|-------|-------|---------------------|
| ANSI – Constant Light | Boost | Power | Mid Power Low Power |
| Light output ¹ [lm] | 2500 | 1000 | 20 |
| Beam distance ¹ [m] | 250 | 170 | 20 |
| Run time ¹ [h] | | 5 | 80 |

SWITCH

Multifunctional Switch

FEATURES

 $\label{eq:def:Dimmable} \mbox{Dimmable , Transportation lock , Flicker Free, Memory Function, Backup Mode}$

TECHNOLOGIES

Advanced Focus System³, Magnetic Charge System, Temperature Control System, Flex Sealing Technology, Cooling Technology, Multi-Core Optics



3 - PRODUCT DATA SHEET V211110

H15R Core

PACKAGING AND LOGISTICS



| PACKAGING INFORMATION | | |
|-----------------------|---|--|
| Type of packaging | Box | |
| Scope of delivery | 1 set of rechargeable batteries, Magnetic charging cable | |
| Item No. | 502123 | |
| Customs tariff number | 85131000000 | |
| Color | black | |
| MSRP price (€) | 169.00 | |

| SINGLE PACKAGE | |
|---------------------------|-----------------|
| Dimensions W x H x D [cm] | 14.5 x 12 x 8.5 |
| Gross weight [g] | 540 |
| GTIN-13 | 4058205020930 |

| EXPORT CARTON | |
|---------------------------|--------------------|
| Unit | 12 |
| Dimensions W x D x H [cm] | 39.5 x 37.5 x 19.5 |
| Gross weight [kg] | 7.25 |
| GTIN-13 | 4058205020954 |



4 - PRODUCT DATA SHEET V211110

H15R Core

ACCESORIES

| PRODUCT CATEGORY | ITEM NUMBER | PRODUCT NAME | MSRP |
|----------------------------|-------------|---|---------|
| Color filter / Signal caps | 502309 | Color Filter Set 47mm | 19.90 € |
| Fastenings / Brackets | 502246 | Adapter for GoPro Type D | 7.90 € |
| Fastenings / Brackets | 502247 | Tripod Adapter Type D | 9.90 € |
| Fastenings / Brackets | 502253 | Belt Clip Type A | 6.90 € |
| Fastenings / Brackets | 502314 | Helmet Connecting Kit Type H | 14.90€ |
| Fastenings / Brackets | 502313 | Helmet Band Fixing Clip Type A | 4.90 € |
| Fastenings / Brackets | 502256 | Universal Mounting Bracket Type E | 12.90 € |
| Battery | 502310 | 2x 21700 Li-ion Rechargeable Battery Pack | 39.90 € |
| Battery | 502411 | Bluetooth® 2x 21700 Batterybox | 59.90 € |
| Charger / Cable | 502265 | Magnetic Charging Cable Type A | 6.90 € |
| Charger / Cable | 502312 | Extension Cable Type C | 9.90 € |
| Fastenings / Brackets | 502451 | Transparent Silicone Headband Type A | 9.90 € |
| Charger / Cable | 502271 | USB Adapter 2.4A | 14.90 € |
| Fastenings / Brackets | 502469 | Headband+Overheadband Core | 9.90 € |
| Fastenings / Brackets | 502470 | Headband+Overheadband Work | 9.90 € |
| Fastenings / Brackets | 502471 | Headband+Overheadband Signature | 12.90€ |



5 - PRODUCT DATA SHEET v211110

H15R Core

PRODUCT SERIES

The Ledlenser H-series offers best-in-class headlamps with reliable lighting that can be used in many applications. The H-series lamps are indispensable for a broad range of users in private and professional environments. The high product quality, the intuitive operation, the ergonomic design and last but not least the unmatched light pattern have led this series to great success. With every product in the H-series being completely redesigned with forward-thinking new technologies and features, Ledlenser has extensively raised the bar with this collection of lights. The new H-series is also the first Ledlenser range of flashlights designed for all user fields. The products of the Core, Work, and Signature range have different designs and features and are therefore tailormade for different target groups.

The Core headlamps are the foundation of the H-series. They can be operated intuitively and offer stepless dimming via the Wheel Switch on the lamp head (except H19R Core). In addition, the headlamps provide an improved constant luminous flux so that the selected brightness can be maintained over a long period of time. Thanks to the Flex Sealing Technology, all models achieve extreme dust and water protection (at least IP67). These and many other features as well as the extensive range of accessories that can be used universally with the Ledlenser Connecting System, make the Core headlamps of the H-series ideal all-rounders for a variety of uses and activities.

FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.

- 1) Measurement values according to ANSI FL1 in the respective setting. If no setting is explicitly indicated, the values refer to luminous flux (lumens/lm) and lighting range (meters/m) on the highest setting, and to battery duration (hours/hrs/h) on the lowest setting. A boost function (if available) can be used several times, but only for short periods of time. If the light is equipped with (a) colored LED(s), the measurement values are given for the white light or the white LED. If the light has different energy modes, the measurement is made based on the "energy saving mode".
- 2) Calculated capacity value in watt-hours (Wh). This applies to the delivery state of the battery/ies inside the respective item, or for lights with rechargeable battery/ies, to the rechargeable battery/ies inside the product when fully charged.
- 3) EP Patent 1880139, US Patent 7,461,960
- 5) Charging time varies by hardware used.

