



— PRODUCT DATA SHEET

iF4R music



iF4R music

PRODUCT DESCRIPTION

Add a little music to your day! We gave our popular spotlight iF4R a special upgrade: The iF4R music has a high-quality speaker built in you can connect your smartphone to and use as a job site radio. Just like the iF4R, the iF4R music has 2500 lumen¹ of light output with five brightness settings. The music spotlight can be charged via magnetic charge system.

- Built-in magnet for easy attachment to metal surfaces (e.g. steel beams)
- Five brightness settings with up to 2500 lumen¹ light output, controlled via multi-function switch
- Built-in speaker with Bluetooth control
- Easy to charge via magnetic charge system
- Large, tough handle for easy transport



TECHNICAL DATA

Width [mm]	235
Depth [mm]	47
Height [mm]	110
Weight incl. batteries [g]	1139
Focus function	No
Primary material	Aluminum alloy
Secondary material	Other plastics
Cartridge	No

POWER SUPPLY

Power source type	Rechargeable battery
Battery quantity	1
Battery type	Li-ion
Battery replaceable	No
Total battery voltage [V]	3.7
Total battery capacity [mAh]	8000
Total battery energy ² [Wh]	29.6
Rechargeable	Yes
Charging time ⁵ [min]	360
Energy status indicator	Battery Indicator, Charge Indicator

FURTHER SPECIFICATIONS

IP class	IP54
Drop test (drop height) [m]	1
Working temperature range [°C]	-10 to +40

LIGHT FUNCTIONS

Low Power, Mid Power, Power

LIGHT SOURCE

Amount LEDs	1
LED type	34W COB LED
Color	White
Color temperature [K]	5400 to 6600
Color rendering index (CRI)	80

LIGHT VALUES

	Boost	Power	Mid Power	Low Power
Light output ¹ [lm]		2500	1000	200
Run time ¹ [h]		1.5	3	15

SWITCH

Multifunctional Switch

FEATURES

Dimmable , Transportation lock , Bluetooth® Speaker

TECHNOLOGIES

Magnetic Charge System

iF4R music

PACKAGING AND LOGISTICS



PACKAGING INFORMATION

Type of packaging	Box
Scope of delivery	Magnetic charging cable, USB power adapter
Item No.	502172
Customs tariff number	94054039900
Color	black
MSRP price (€)	189.00

SINGLE PACKAGE

Dimensions W x H x D [cm]	30.7 x 11.8 x 5.2
Gross weight [g]	1356
GTIN-13	4058205020268

EXPORT CARTON

Unit	6
Dimensions W x D x H [cm]	27.2 x 18.9 x 35.5
Gross weight [kg]	8.456
GTIN-13	4058205020282

iF4R music

ACCESORIES

PRODUCT CATEGORY	ITEM NUMBER	PRODUCT NAME	MSRP
Charger / Cable	502265	Magnetic Charging Cable Type A	6.90 €
Charger / Cable	502271	USB Adapter 2.4A	14.90 €
Charger / Cable	0380	USB Car Charger	9.90 €

iF4R music

PRODUCT SERIES

The Ledlenser i-Series Work lights & spotlights

Powerful performance! Ready whenever you need to illuminate the darkness of your workshop or construction site: the Ledlenser i-Series work lights and spotlights - durable multi-purpose lights for true professionals! Whether you use a single spotlight or floodlight with wide coverage, with these professional lights you always have the right type of light at your fingertips. Compact, powerful and rechargeable - each model impresses during everyday use.

FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.

1) Measurement values according to ANSI FL1 in the respective setting. If no setting is explicitly indicated, the values refer to luminous flux (lumens/lm) and lighting range (meters/m) on the highest setting, and to battery duration (hours/h) on the lowest setting. A boost function (if available) can be used several times, but only for short periods of time. If the light is equipped with (a) colored LED(s), the measurement values are given for the white light or the white LED. If the light has different energy modes, the measurement is made based on the "energy saving mode".

2) Calculated capacity value in watt-hours (Wh). This applies to the delivery state of the battery/ies inside the respective item, or for lights with rechargeable battery/ies, to the rechargeable battery/ies inside the product when fully charged.

4) Warranty period of five years from the date of purchase, seven years if the product is registered online on our website. The warranty is valid worldwide and legal warranty rights also apply. It covers defects in materials and workmanship. For the proper functioning of rechargeable batteries a different warranty period of 24 months applies. Excluded from this warranty are the product series "Solidline", Ledlenser K1 and Ledlenser K2. The warranty does not apply to Defects in batteries, holsters, pouches, remote switches, color filters, imprints or surface coatings. The guarantor is Ledlenser GmbH & Co. KG, Kronenstr. 5 - 7, 42699 Solingen, Germany. More information: ledlenser.com/warranty

5) Charging time varies by hardware used.