

LED Downlights



VT-8017

HIGHLIGHTS :

WATTS



12

EQ. WATTS



60

LUMINOUS



800

BEAM ANGLE



360

| | | |
|----------------------------|---|-----------------------|
| Item No | : | VT-8017 |
| SKU Code | : | 5057 |
| Watts | : | 12 |
| EQ. Watts | : | 60 |
| Voltage | : | 110-240V,50/60Hz |
| Lumen(lm) | : | 800 |
| Color Temperature | : | 3000K |
| Beam Angle | : | 360 |
| Commercial type | : | ROUND |
| PF | : | >0.7 |
| LED Chip Type | : | SMD |
| CRI | : | >80 |
| Energy rating label | : | A++ |
| IP Rating Protection Class | : | IP20 |
| Body type | : | PLASTIC CLAD ALUMINUM |
| Dimmable | : | No |
| Operation Temperature | : | -20~50'C |
| EAN code | : | 3800157605250 |
| Unit size | : | 290 x 60mm |
| Packing details | : | 10.00 |
| Unit cbm | : | 0.00700 |

PRODUCT FEATURES

- Innumerable styles & Elegant appearance
- Non - Flickering
- No UV Radiation
- Premium Quality Power Driver with lowest power factor saver & high RA
- Varied finishes with strong die cast Aluminium body
- Residences, Showrooms, Hotels & Boutiques etc.