

DISSIPATIVE LIGHT GLOVES

51-690-02xx, 51-690-12xx

Properties

| | |
|---------------------|---|
| Usage category: | General purposes |
| Configuration: | Elastic wrists, Coating on finger tips |
| Fabric: | Textured Nylon 87% Polyurethane 6% Elastic 4% Polyester 3% |
| Colour: | white |
| Shelf life: | functional 1 year |
| Washable: | not washable |
| Surface resistance: | $< 10^9 \Omega$ |
| Coating: | solvent based, foamed polyurethane |
| Packaging: | 10 pairs/bag |
| Compliance: | IEC 61340/EN1149 |



Size, dimensions and part numbers

| Part Number White version | Part Number Grey version | Size | Length |
|------------------------------|-----------------------------|------|----------------|
| 51-690-0200 | 51-690-1200 | S | 190 mm +/-20mm |
| 51-690-0205 | 51-690-1205 | M | 200 mm +/-20mm |
| 51-690-0210 | 51-690-1210 | L | 210 mm +/-20mm |
| 51-690-0215 | 51-690-1215 | XL | 220 mm +/-20mm |
| 51-690-0220 | 51-690-1220 | XXL | 230 mm +/-20mm |

Caution:

If you feel itchiness or develop a rash, discontinue use. The unique design of these gloves makes them extremely clean, however they are not completely lint-free. Not washable because the ESD may be washed away / damaged. This product is not advisable to be used in working environment that has contact with water or liquid.