

FEATURES

- Hex nuts metric
- To DIN934
- A2 grade 18/8 stainless steel (Type 304 S15)
- Good resistance to corrosion
- Easy to tighten and loosen

RS PRO Stainless Steel, Hex Nut, M8

RS Stock No.: 530-769



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

RS PRO hex nuts are a six-sided nut that fastens screws and bolts efficiently and securely. They are the most common hexagonal fastener that has internal threads that screw on to the shank of a bolt or a hex cap screw. These metric hex nuts are available in a variety of sizes ranging from M2 to M20. These RS PRO hex nut fasteners come in various thread sizes:

527-218 - M2

527-224 - M2.5

527-230 - M3

527-246 - M3.5

527-252 - M4

527-268 - M5

527-274 - M6

530-769 - M8

530-775 - M10 530-781 - M12

275-670 - M16

275-686 - M20

General Specifications


Thread Size	M8
Material	Stainless Steel
Туре	Full
Finish	Plain
Applications	Automotive applications, Construction industry, Machinery & workshops, DIY enthusiasts and professionals, Use in manufacturing sectors such as the food industry, Home



Mechanical Specifications

Width	13mm	
Stainless Steel Type	304 (A2)	
Specification	DIN 934, ISO 4032	
Thickness	6.44mm to 6.8mm	
Thread Pitch	1.25mm	
Width Across Corners	14.38mm	
Width Across Flats	12.73mm to 13mm	





RS Part No.	Thread Size
275670	M16
275686	M20
527218	M2
527224	M2.5
527230	M3
527252	M4
527268	M5
527274	M6
530769	M8
530775	M10
530781	M12
1839045	M12 (19mm)