

FEATURES

- **Stainless steel construction**
- **Lightweight return spring**
- **25mm long stainless steel jaws**
- **Moulded plastic grip handles**
- **Overall length 130mm**

RS PRO 130mm Stainless Steel Flat Nose Pliers With 25mm Jaw Length

RS Stock No.: 536-341



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted RS PRO brand, these stainless steel pliers are lightweight and versatile, and so are perfect for precision applications. The pliers feature moulded plastic bow handles for an assured grip, with spring action return to reduce fatigue over long periods of use.

General Specifications

Plier Type	Flat nose pliers
Tip Style	Straight
Material	Stainless steel sheet (#420-j2) for plier, pivot, Spring steel for tension return spring, PVC injection handle
Finish	Grinding-vibration finish for plier, Chrome plated rivets, Blue colour handle
Applications	Electricians, technicians, maintenance engineers

Mechanical Specifications

Jaw Length	25mm
Overall Length	130mm
Hardness	Heat treated to hrc:46~50(body) Pivot--hrc:20~25

