

## FEATURES

- Two sets: 9 piece ballpoint set and a 7 piece foldable set
- Heat treated, tempered alloy steel gives the key phenomenal strength and resistance to rotational distortion
- Make use of both ends of the hex keys
- Portable and stylish

## RS PRO 16 pieces Hex Key Set, L Shape 1.5mm Ball End, Hex Wrench

RS Stock No.: 542-3492



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

From RS PRO, this high-quality hex key set comes in two separate holders- one in a convenient pen-knife style holder, and one in a handy fold-out holder to keep differing allen key sizes all in one place. This versatile key set are portable, neatly organized and ready for any task.

### General Specifications

<b>Imperial or Metric</b>	Metric
<b>Number of Pieces</b>	16
<b>Shape</b>	L
<b>Hex Key Type</b>	Ball End ,Hex Wrench
<b>Material</b>	Alloy Steel
<b>Finish</b>	
<b>Height Safe</b>	No
<b>Set Contents</b>	16pc. Metric ball end long Arm hex key wrenches
<b>Applications</b>	They are ideal for when fasteners need to be adjusted or equipment needs to be dismantled. From furniture assembly to bicycle maintenance

### Electrical Specifications

<b>Non-Sparking</b>	No
---------------------	----

### Mechanical Specifications

<b>Short or Long Arm</b>	Long
<b>Hardness</b>	Heat treated hex key to HRC 50 to 70
<b>Working Angle</b>	25°

### Dimensions

Hex Key Size(Ball Point Set)		Hex Key Size(Foldable Set)	Hex Key Size(Foldable Set)
Metric	Imperial	Metric	Imperial
1.5mm	1/16in	2.0mm	5/64in
2.0mm	5/64in	2.5mm	3/32in
2.5mm	3/32in	3mm	1/8in
3mm	1/8in	4mm	5/32in
4mm	5/32in	5mm	13/64in
5mm	13/64in	6mm	15/64in
6mm	15/64in	8mm	5/16in
8mm	5/16in		
10mm	25/64in		

### Approvals

Compliance/Certifications	ISO2936 (formerly DIN 911L)
VDE/1000V Approved	No



