

FEATURES

- Self-tapping screw with hexagonal head
- Zinc-plated steel for corrosion protection in indoor applications
- Flange head to distribute the load
- To DIN 7504

RS PRO Bright Zinc Plated Steel Self Drilling Screw M5.5 x 38mm Long

RS Stock No.: 546-5913



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted RS PRO brand, these zinc plated and passivated hardened steel Self-drilling screws offer all the advantages associated with standard self-tapping screws but are capable of drilling their own pilot holes into sheet metal up to 5mm in thickness. As it has a flange head, it doesn't require a washer to distribute the pressure of the nut.

General Specifications

Drive Type	Hex
Head Shape	Hex Washer
Applications	Light And Heavy Gauge Sheet Metals, Soft Plastics, Heating And Air Conditioning, Metal And Fiberglass Fabrication Industries

Mechanical Specifications

Length Metric	38mm
Material	Steel
Thread Size (mm)	5.5mm
Thread Size (Metric)	M5.5
Finish	Bright Zinc Plated

Approvals

Compliance/Certifications	DIN 7504
----------------------------------	----------



RS Part No.	Thread Size	Length
5465806	4.2mm	13mm
5465812	4.2mm	19mm
5465834	4.8mm	16mm
5465856	4.8mm	19mm
5465862	4.8mm	25mm
5465878	5.5mm	19mm
5465884	5.5mm	25mm
5465890	5.5mm	32mm
5465913	5.5mm	38mm
5465929	6mm	60mm
5465935	6mm	1/2in
5465941	6mm	3/4in
5465957	8mm	3/4in
5465979	8mm	1/2in
5465985	8mm	1in
5466001	10mm	3/4in
5466017	10mm	1in

