

FEATURES

- **3 Stage Control (Fast/Normal/Float)**
- **Full Charge with Automatic Shutdown**
- **Short Circuit Output Protected**
- **Reverse Polarity Protected**
- **Overload Protected**
- **Compliant to safety standards**

RS PRO Lead Acid 12V 25A Battery Charger with EUplug

RS Stock No.:549-306



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The high-quality range of Automatic 3 Stage 12V Lead Acid Battery Chargers from our own RS PRO brand benefits from charging current of 2~50A and aluminium impact resistant casing. It is also supplied with UK and EU Mains Leads & Crocodile Clip Connectors

General Specifications

Number of Batteries Charged	1
Chemistries Charged	Lead Acid
Batteries Included	No

Electrical Specifications

Input Voltage	230V ac
Plug Type	EU
Number of Charge Stages	3

Output Data	
Charge Current	25A
Output Voltage	12V
Output Connectors	Crocodile Clip Connectors.

Mechanical Specifications

Dimensions	275mm x 186mm x 76mm
Weight	2.9kg

Approvals

Compliance/Certifications

2011/65/EU and 2015/863



