

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0551000670](#)
Status: **Active**
Overview: [2.00mm I/O Connectors](#)
Description: 2.00mm Pitch Serial I/O Connector, Plug Kit, Wire-to-Wire, Solder Type, 6 Circuits, Bag

Documents:

[3D Model](#) [Application Specification 551000680AS-A00 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-54280-005-001 \(PDF\)](#)

General

Product Family	I/O Connectors
Series	55100
Application	Wire-to-Wire
Component Type	Plug
Overview	2.00mm I/O Connectors
Product Name	2.00mm I/O Connectors
Type	N/A
UPC	822348181865

Physical

Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black, Gray
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze, Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic, Polycarbonate
Net Weight	9741.381/mg
Orientation	Vertical
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.032µm
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	N/A
Wire Insulation Diameter	2.10mm max.
Wire Size AWG	16, 18, 20, 22, 24, 26, 28


Electrical

Current - Maximum per Contact	2.0A
Shielded	Yes
Voltage - Maximum	125V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	551000680AS-A00
Product Specification	PS-54280-005-001
Sales Drawing	SD-54280-011-001, SD-55100-004-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[55100 Series](#)

Mates With

2.00mm Pitch IEEE 1394-1995 I/O PCB
Socket [534620629](#)
2.00mm Pitch Serial
I/O Connector [542800609](#) , [5006550609](#) ,
[5006550619](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION