

SOLID PC 5628 13 T



Sample photo

Order symbol: PC 5628 13 T
Product nbr: 5330064
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074005595
EI. number:
 Finland: 3423821
 Electric No. Italy: 7402060
 Electric No. Sweden: 2539456

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	558	278	130	EKTX	Mounting plate isolated
inch:	22.0	10.9	5.1	EKV 22	DIN-35 Mounting rail
				EKV 50	DIN-35 Mounting rail
				EKTZR	Extension frame

Materials:

Material: Polycarbonate
Base colour: RAL 7035 -light grey
Cover screws material: Polyamide
Cover colour: Clear transparent
Cover screws colour: Grey
Gasket material: Polyurethane

Rating:

Ingress Protection (EN 60529): IP66/IP67
 Impact Resistance (EN 62262): IK08/IK09
 Electrical insulation: Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): 1
 UV resistance: UL 508
 Flammability Rating: UL 746C 5"
 Glow Wire Test (IEC 695-2-1) °C: 960
 NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Temperatures:

Temperature °C (short term): -40 ... 120 °C
Temperature °C (continuous): -40 ... 80 °C
Temperature °F (short term): -40 ... 250 °F
Temperature °F (continuous): -40 ... 175 °F

Certificates:

SGS Fimko
 Gost R

Accessories:

EKTVT Mounting plate

