

FEATURES

- Ceramic cartridge
- T Speed rated
- 5mm x 20mm cartridge size

RS PRO, 3.15A Ceramic Cartridge Fuse, 5 x 20mm, Speed T

RS Stock No.: 563-699



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Cartridge Fuses



Product Description

RS PRO anti-surge ceramic cartridge fuses which are designed to prevent damage to electrical equipment. These fuses allow an electric current to flow through until the current goes over the fuses rating then it will blow and stop the flow of electricity. This range of ceramic cartridge fuses are 5 x 20mm with a T speed rating.

RS PRO cartridge fuse packs are available in a range of current ratings with varying resistance values to suit all your requirements. This range is reliable for a broad range of applications.

General Specifications

Fuse Speed	Т
Body Material	Ceramic
Applications	Industrial, Commercial, Home/Residential, Automotive

Electrical Specifications

Current Rating	3.15A
Voltage Rating	250V ac
High Rupture Capacity	Yes
Breaking Capacity (at Maximum Voltage Rating)	1500A

Mechanical Specifications

Fuse Size	5mm x 20mm
Overall Length	20 mm
Diameter	5mm



Operation Environment Specifications

Maximum Operating Temperature	125°C
Minimum Operating Temperature	-55°C

Approvals

Compliance/Certifications	SEMKO,BSI, VDE, CSA, MITI
---------------------------	---------------------------



