

BULL BAR INDEXING DECKING REMOVAL TOOL

- Double fork design provides balanced lift on both sides of the nail for faster, cleaner, lower-effort board removal
- Rugged indexing joint allows for maximum flexibility and increased leverage
- Precision tips designed for fast access between boards and reduced damage for reclaiming materials
- Gripping teeth on forks assist in preventing board slippage
- Center nail puller allows better balance and more leverage



CATALOG NO.	TIP LENGTH	TIP WIDTH	OVERALL LENGTH	PRODUCT WEIGHT KG
DKB446X	115 mm	140 mm	1118 mm	3,47

CODE RED™ INDEXING FLAT RENOVATION BARS

- Head indexes through an arc of over 180° and locks in 15 positions for maximum access
- Angled head with nail slot for prying and pulling nails or boards
- Extra-wide prying end prevents damage by spreading the prying force
- Raised heavy-duty striking surface on the head to assist in demolition
- Solid construction withstands wear, pressure, and damage
- Full steel body for increased durability and longer product life
- Heat-treated striking face
- Durable two-tone grip provides comfort, control, and slip prevention



CATALOG NO.	TIP LENGTH	TIP WIDTH	OVERALL LENGTH	PRODUCT WEIGHT KG
DB18X	95 mm	55 mm	457 mm	1,20
DB30X	95 mm	55 mm	762 mm	1,86

CODE RED™ ADJUSTABLE PRY BARS

- Adjustable jaws slide and clamp to fit onto objects for straightening and prying
- Large claw on head adjusts for best leverage when pulling nails
- Crow bar end with nail puller slot
- Hammer head surface for striking



CATALOG NO.	TIP LENGTH	TIP WIDTH	OVERALL LENGTH	PRODUCT WEIGHT KG
DB16	127 mm	44 mm	406 mm	1,67
DB24	127 mm	44 mm	610 mm	2,01

INDEXING NAIL PULLER

- Indexing head with 14 locking positions for quick angle adjustment up to 180 degrees for optimized leverage
- Striking face allows for claw to be driven under nails that are under the surface
- Designed to reach between studs, joists, and other obstructions
- Ergonomic, contoured handle for superior grip and user safety



CATALOG NO.	TIP LENGTH	TIP WIDTH	OVERALL LENGTH	PRODUCT WEIGHT KG
DB12NP	67 mm	23 mm	320 mm	0,51

NAIL PULLER

- Forged alloy box-joint and hardened, tempered jaw
- Black enamel finish offers extra durability
- Works great on flush, hard-to-grip nails
- Ideal for remodeling or renovation projects
- 16 penny nail jaw capacity
- 19 in length and 24 in full extension



CATALOG NO.	TIP LENGTH	TIP WIDTH	CONT. LENTH	EXT. LENGTH	PRODUCT WEIGHT KG
56	28 mm	6 mm	483 mm	610 mm	1,91

76 77