

## LED Floodlights



### VT-4955

#### HIGHLIGHTS :

WATTS



50

EQ. WATTS



250

LUMINOUS



4250

BEAM ANGLE



100

|                            |                    |
|----------------------------|--------------------|
| Item No                    | : VT-4955          |
| SKU Code                   | : 5826             |
| Watts                      | : 50               |
| EQ Watts                   | : 250              |
| Voltage                    | : 220-240V,50/60Hz |
| Lumen(lm)                  | : 4250             |
| Color Temperature          | : 4500k            |
| Beam Angle                 | : 100              |
| PF                         | : >0.9             |
| LED Chip Type              | : SMD 2835         |
| CRI                        | : >70              |
| Energy rating label        | : A+               |
| Certification              | : EMC,LVD,ROHS     |
| IP Rating Protection Class | : IP65             |

|                       |                     |
|-----------------------|---------------------|
| Body type             | : DIE CAST ALUMINUM |
| Dimmable              | : No                |
| Life Time             | : 20,000 HOURS      |
| Operation Temperature | : -25 ~50°C         |
| EAN code              | : 3800157615006     |
| Unit size             | : 194*237mm         |
| Packing details       | : 10                |
| Unit cbm              | : 0.004032          |

#### PRODUCT FEATURES

- Available in White , Warm White and RGB Light output option
- Premium Quality Aluminium Alloy body
- Corrosion Resistant
- Built in Power supply, No external ballast required
- PIR Sensor Movement Detector – Optional
- Widely used for Lighting Driveways, Gardens & Buildings, Commercial Bill,Boards & Hoardings, Plazas,Sports Grounds & Parking Lots

[CLICK HERE](#)  
FOR OTHER RELATED CERTIFICATES