

## LED Floodlights



### VT-4955

#### HIGHLIGHTS :

WATTS



50

EQ. WATTS



250

LUMINOUS



4250

BEAM ANGLE



100

Item No	: VT-4955
SKU Code	: 5827
Watts	: 50
EQ Watts	: 250
Voltage	: 220-240V,50/60Hz
Lumen(lm)	: 4250
Color Temperature	: 6000K
Beam Angle	: 100
PF	: >0.9
LED Chip Type	: SMD 2835
CRI	: >70
Energy rating label	: A+
Certification	: EMC,LVD,ROHS
IP Rating Protection Class	: IP65

Body type	: DIE CAST ALUMINUM
Dimmable	: No
Life Time	: 20,000 HOURS
Operation Temperature	: -25 ~50°C
EAN code	: 3800157615013
Unit size	: 194*237mm
Packing details	: 10
Unit cbm	: 0.002895

#### PRODUCT FEATURES

- Available in White , Warm White and RGB Light output option
- Premium Quality Aluminium Alloy body
- Corrosion Resistant
- Built in Power supply, No external ballast required
- PIR Sensor Movement Detector – Optional
- Widely used for Lighting Driveways, Gardens & Buildings, Commercial Bill,Boards & Hoardings, Plazas,Sports Grounds & Parking Lots

[CLICK HERE](#)  
FOR OTHER RELATED CERTIFICATES