

INSTA contactor With 3 NO contacts + 1 NC contact Contact for 230 V AC, 400V 40A Control 24 V AC



Model	
Product brand name	SENTRON
Product designation	Insta contactors
Design of the product	3 NO contacts 1 NC contact
Type of voltage / of the operating voltage	AC
Type of voltage / for actuation	AC
Protection class	
Protection class IP	IP20
Switching capacity	
Switching capacity active power / with filament lamp load	4 000 W
Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	4 W
Electricity	
Current / at AC / rated value	40 A
Main circuit	

Operating voltage / rated value	
<ul style="list-style-type: none"> • minimum • maximum 	440 V
Operating current / rated value	40 A

Control current

Control supply voltage	
<ul style="list-style-type: none"> • rated value • rated value / maximum 	24 V
	24 V

Product details

Product component / Slide for manual operation	No
Product extension / can be installed / supplementary devices	Yes

Number

Number of NC contacts	1
Number of NO contacts	3

Mechanical Design

Height	90 mm
Width	54 mm
Depth	71 mm
Installation depth	64 mm
Number of width units	3
Net weight	398 g

Certificates

Reference code / acc. to DIN EN 61346-2	Q
---	---

General Product Approval	Declaration of Conformity	other
--------------------------	---------------------------	-------



[Miscellaneous](#)



[Environmental Confirmations](#)

Further information

- Information- and Downloadcenter (Catalogs, Brochures,...)**
<http://www.siemens.com/lowvoltage/catalogs>
- Industry Mall (Online ordering system)**
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TT5841-2>
- Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**
<https://support.industry.siemens.com/cs/ww/en/ps/5TT5841-2>
- Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT5841-2
- CAX-Online-Generator**
<http://www.siemens.com/cax>

