EAO – Your Expert Partner for Human Machine Interfaces

61-6441.4057 - Emergency-stop switch compact, foolproof EN IEC 60947-5-5

61-6441.4057 - Emergency-stop switch compact, foolproof EN IEC 60947-5-5



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting Mounting cut-out

Design

Front Front shape Front dimension

Other Attributes Marking Weight

Operating-/Indication part Lens material

Lens colour Lens profile

IP-Rating Front protection

Connection Method Terminal

Actuator Switching action

Switching element Contacts

2 NC

Ø 16 mm

raised

round

Ø 27 mm

Arrows

Plastic

Mushroom

IP67, IP69K

Maintain

Solder 2.8 x 0.5 mm

red

0.018 kg


Function Emergency stop switch



EAO – Your Expert Partner for Human Machine Interfaces


61-6441.4057 - Emergency-stop switch compact, foolproof EN IEC 60947-5-5

Dimensions




L1 = Solder/Plug-in terminal 2.8 x 0.5 mm

Mounting cut-outs



Wiring diagram



Component layout



Additional information

Twist to unlock clockwise Position indication ring green Application as per DIN EN ISO 13850 and EN 60204-1

Legend Switching action: C = Maintained

