EAO – Your Expert Partner for **Human Machine Interfaces**

61-6461.4047 - Emergency-stop switch compact, foolproof EN IEC 60947-5-5

61-6461.4047 - Emergency-stop switch compact, foolproof EN IEC 60947-5-5



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

 $\begin{array}{ll} \mbox{Mounting cut-out} & \mbox{\varnothing 16 mm} \\ \mbox{Design} & \mbox{raised} \end{array}$

Front

Front shape round Front dimension Ø 40 mm

Other Attributes

Marking Arrows Weight 0.018 kg

Operating-/Indication part

Lens material Plastic
Lens colour red
Lens profile Mushroom

IP-Rating

Front protection IP67, IP69K

Connection Method

Terminal Solder 2.8 x 0.5 mm

Actuator

Switching action Maintain

Switching element

Contacts 1 NC

Function


Emergency stop switch

e a o

EAO – Your Expert Partner for **Human Machine Interfaces**


61-6461.4047 - Emergency-stop switch compact, foolproof EN IEC 60947-5-5

Dimensions




L1 = Solder/Plug-in terminal 2.8 x 0.5 mm

Mounting cut-outs



Wiring diagram



Component layout



Additional information

Twist to unlock clockwise Position indication ring green Application as per DIN EN ISO 13850 and EN 60204-1

Legend

Switching action: C = Maintained