

Datasheet

Leveling Castor - RS 6114414

ENGLISH





ISO view

Side view

Bracket

- Forged steel plate with khaki powder coating
- Aluminum die-casting bracket with bi-level balls in the swivel head
- High quality ABS resin handle, two side access to level
- NBR resin cushion to stand, anti-vibration function
- Ivory texture powder coating and zinc-galvanized

Wheels


- ▶ High quality nylon
- HIgh abrasion resistance, shock and impact-resistant, corrosionresistant, high chemical resistance to alcohol, salts and certain acids, black color
- ▶ No bearing

Technical Data

Wheel Diameter	50 mm
Width of Tread	25 mm
Hardness of Tread	70 Shore D
Center Bolt	M12 x 1.75P or M16 x 2.0P
Bolt Length	18 mm
Leveling Extent	10 mm
Offset	36 mm
Overall Height	82 mm
Temperature	-10 ~ +90 °C
Load Capacity / 1pcs	250 kg
Load Capacity / 4pcs	500 kg

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.





ENGLISH

