


FEATURES

- Welded, exposed junction for fast response times
- Glassfibre insulated cable
- Conforms to IEC 60584

RS PRO Type K Thermocouple 0.3mm Diameter → +600°C

RS Stock No.: 621-2170



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From RS Pro a range of Type J, K, T & N wire type thermocouple temperature sensors conforming to IEC 60584 standards. These thermocouples have a welded exposed hot junction for a fast response time and cable conductors surrounded by a glassfibre insulation.

General Specifications

Thermocouple Type	Type K
Temperature Measurement Range	-50°C to 600°C
Construction	Fine Wire Sensor
Measuring Junction	Exposed
Accuracy	±1.5°C
Output	100°C =4.096mV
Response Time	0.7s
Seebeck Coefficient	41μV/°C
Maximum Voltage	48.838mV
Transmitter	None
Calibration Availability	Yes
Application	Universal, measurement simple and economic, ideal for testing measures temperature or laboratory.

Mechanical Specifications

Probe Diameter	0.3mm
Insulation / Sheath Material	Glass Fibre
Termination Type	Cable Gland
Terminal Head	17mm x 11mm
Compensating Cable Length	2m
Cable Insulation	PVC
Weight	8.33g



Approvals

Compliance/Certifications	IEC 60584
Standards Met	RoHS Compliant





T/C Type	Conductors	Length	Termination	+Positive tail wire	-Negative tail wire code	Allied Code	RS order Code
'K'	1/0.2mm	1 metre	Mini plug	Green	White	70643600	363-0250
'K'	1/0.2mm	2 metre	Mini plug	Green	White		110-4482
'K'	1/0.2mm	5 metre	Mini plug	Green	White		123-6306
'K'	1/0.2mm	10 metre	Mini plug	Green	White		123-6307
'' '' '' ''	1/0.2mm 1/0.2mm 1/0.2mm 1/0.2mm	1 metre 2 metre 5 metre 10 metre	Mini plug Mini plug Mini plug Mini plug	Black Black Black Black	White White White	70643599	363-0244 123-6308 123-6309 123-6310
'T'	1/0.2mm	1 metre	Mini plug	Brown	White	70643601	363-0266
'T'	1/0.2mm	2 metre	Mini plug	Brown	White		123-6311
'T'	1/0.2mm	5 metre	Mini plug	Brown	White		123-6312
'T'	1/0.2mm	10 metre	Mini plug	Brown	White		123-6313



T/C	Туре	Conductors	Cores	Reel Length	Allied code	RS order code
J		1/0.2mm	+Black/-White	25 metres	70657194	827-5980
j		1/0.2mm	+Black/-White	50 metres	70657195	827-5984
		•				
J		1/0.315mm	+Black/-White	25 metres	70657198	827-5993
J		1/0.315mm	+Black/-White	50 metres	70657199	827-5996
K		1/0.315mm	+Green/-White	25 metres	70657200	827-6000
K		1/0.315mm	+Green/-White	50 metres	70657205	827-6019
Т		1/0.315mm	+Brown/-White	25 metres	70657208	827-6028
Т		1/0.315mm	+Brown/-White	50 metres	70657206	827-6022
J		1/0.508mm	+Black/-White	25 metres	70657197	827-5990
J		1/0.508mm	+Black/-White	50 metres	70657201	827-6003
K		1/0.508mm	+Green/-White	25 metres	70657203	827-6012
K		1/0.508mm	+Green/-White	50 metres	70657204	827-6016
J		7/0.2mm	+Black/-White	25 metres	70657202	827-6006
K		7/0.2mm	+Green/-White	25 metres	70657207	827-6025
Т		7/0.2mm	+Brown/-White	25 metres	70657209	827-6031
N		7/0.2mm	+Pink/-White	25 metres	70657210	827-6034
	Conductor	rs Cores	Jacket	Reel Length	Allied Code	RS order code
Exten		. 6 / 14/	hita Gran	10	70557004	027 5645
KX KX	7/0.2mm 7/0.2mm	+Green/-W +Green/-W		10 metres 25 metres		827-5615 236-3820
KX	7/0.2mm	+Green/-W		50 metres		827-5619
KX	7/0.2mm	+Green/-W		100 metres		611-7889
KX	7/0.2mm	+Green/-W	hite Green	200 metres	70657088	827-5628
JX	7/0.2mm	+Black/-Wh		10 metres		219-4753
JX	7/0.2mm	+Black/-Wh		25 metres		827-5592
JX JX	7/0.2mm 7/0.2mm	+Black/-Wh +Black/-Wh		50 metres 100 metres		827-5596 236-3915
JX	7/0.2mm	+Black/-Wh		200 metres		827-5606
TX	7/0.2mm	+Brown/-W	/hite Brown	10 metres	70641637	219-4703
TX	7/0.2mm	+Brown/-W		25 metres		236-3870
TX	7/0.2mm	+Brown/-W		50 metres		827-5653
TX	7/0.2mm	+Brown/-W		100 metres		762-1146
TX	7/0.2mm	+Brown/-W	hite Brown	200 metres	70657098	827-5662
NX	7/0.2mm	+Pink/-Whi	te Pink	10 metres	70641635	219-4668
NX	7/0.2mm	+Pink/-Whi		25 metres		827-5637
NX NX	7/0.2mm 7/0.2mm	+Pink/-Whi +Pink/-Whi		50 metres		827-5631 827-5640
MV	7/U.ZIIIII	TPHIK/-VVIII	te Pink	100 metres	70657092	027-3040



	Conductors	Cores	Jacket	Reel Length	Allied		RS orde	er code
Compensating:					Coue			
VX (KCB)	7/0.2mm	+Green/-White	Green	10 metres	7065	7082	827-560	09
VX (KCB)	7/0.2mm	+Green/-White	Green	25 metres	7064	1629	219-4551	
VX (KCB)	7/0.2mm	+Green/-White	Green	50 metres	7065	7080	827-560	03
VX (KCB)	7/0.2mm	+Green/-White	Green	100 metres	7064	1630	219-45	73
VX (KCB)	7/0.2mm	+Green/-White	Green	200 metres	7065	7083	827-56	12
VX (KCB)	13/0.2mm	+Green/-White	Green	10 metres	7065	7086	827-562	21
VX (KCB)	13/0.2mm	+Green/-White	Green	25 metres	7065		827-562	
VX (KCB)	13/0.2mm	+Green/-White	Green	50 metres	7065		827-563	
VX (KCB)	13/0.2mm	+Green/-White	Green	100 metres	7065		762-11	52
U (RCA)	7/0.2mm	+Orange/-White	Orange	10 metres	7065	7096	827-56	56
U (RCA)	7/0.2mm	+Orange/-White	Orange	25 metres	7064		611-790	
U (RCA)	7/0.2mm	+Orange/-White	Orange	50 metres	7065		827-56	
U (RCA)	13/0.2mm	+Orange/-White	Orange	10 metres	7064	16/11	219-476	50
U (RCA)	13/0.2mm	+Orange/-White	Orange	25 metres	7065		827-564	
U (RCA)	13/0.2mm	+Orange/-White	Orange	50 metres	7065		827-564	
o (nea)	15/0.211111	Torange, Write	Ordrige	30 metres	7003	1034	027-30-	•
T/C Type	Conductors	Cores	Jacket	Reel Len	gth	Allied		RS order code
						code		
Extension:								
KX	7/0.2mm	+Yellow/-Red	Yellow	25 m		706561	.02	814-0018
KX	7/0.2mm	+Yellow/-Red	Yellow	100 m		706561	.05	814-0027
KX	7/0.2mm	+Yellow/-Red	Yellow	200 m		706561		814-0020
JX	7/0.2mm	+ White/-Red	Black	25 m		706560	96	813-9995
JX	7/0.2mm	+ White/-Red	Black	100 m		706560	98	814-0005
JX	7/0.2mm	+ White/-Red	Black	200 m		706560		814-0008
TX	7/0.2mm	+Blue/-Red	Blue	25 m		706561	19	814-0074
TX	7/0.2mm	+Blue/-Red	Blue	100 m		706561		814-0083
TX	7/0.2mm	+Blue/-Red	Blue	200 m		706561		814-0086
Compensating	•	-						
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	25 m		706561	27	814-0103
	7/0.2mm	+Yellow/-Red	Yellow	100 m		706561		814-0103
VX (KCB)								
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	200 m		706561	.31	814-0115



T/C Type KX	Conductors 1/0.2mm	Cores +Yellow/-Red	Reel Length 25 metres	Allied code 70656106	RS order code 814-0030
KX	1/0.2mm	+Yellow/-Red	50 metres	70656111	814-0049
KX	1/0.2mm	+Yellow/-Red	100 metres	70656109	814-0042
KX	7/0.2mm	+Yellow/-Red	25 metres	70656110	814-0046
KX	7/0.2mm	+Yellow/-Red	50 metres	70656113	814-0055
KX	7/0.2mm	+Yellow/-Red	100 metres	70656114	814-0058
KX	1/0.3mm	+Yellow/-Red	25 metres	70656104	814-0024
KX	1/0.3mm	+Yellow/-Red	50 metres	70656107	814-0033
KX	1/0.3mm	+Yellow/-Red	100 metres	70656108	814-0036
TX	1/0.3mm	+Blue/-Red	25 metres	70656121	814-0080
TX	1/0.3mm	+Blue/-Red	50 metres	70656126	814-0099
TX	1/0.3mm	+Blue/-Red	100 metres	70656124	814-0092
TX	1/0.2mm	+Blue/-Red	25 metres	70656125	814-0096
TX	1/0.2mm	+Blue/-Red	50 metres	70656128	814-0106
TX	1/0.2mm	+Blue/-Red	100 metres	70656129	814-0109