

FEATURES

- Aluminium alloy LM24 to BS 1490 with 75-100 microns thick nylon coating
- Self adhesive neoprene seal included to provide IP66 protection
- Coating not affected by drilling or machining

RS PRO General Purpose Enclosures - Die Cast Aluminium Enclosure

RS Stock No.: 621-5012



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

IP66 Flanged - Nylon Coated

This RS Pro Aluminium Enclosure is Nylon coated and has flanges for housing electrical components. Can be wall mounted or mounted on a place of installation. Made of Aluminium alloy ADC-12 with a stove acrylic finish. With an IP66 seal, this enclosure is dust proof, splash proof and protects from powerful jets of water.

General Specifications

Body Material	Die Cast Aluminium
Colour	Black
Lid Colour	Black
Handheld	No
Flanged	Yes
Shielded	Yes
Transparent Door	No

Mechanical Specifications

Gasket Material	Neoprene
External Height	30mm
External Length	139.7mm
External Width	63.8mm
External Dimension	139.7mm x 63.8mm x 30mm
Thickness	75-100 Micron

Protection Category	
IP Rating	IP66
Approvals	
Declarations	RoHS Certificate of Compliance

Similar Products

Stock No.	Brand	Product Name	Body Material	Colour	Shielded
517-3333	RS PRO	Die Cast Aluminium Enclosure	Die Cast Aluminium	Natural	Yes

General Purpose Enclosures



Aluminium Aluminium Natural Enclosure		
--	--	--

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws

