

ENGLISH

Datasheet

RS Pro Swivel Plate Castor ART36 200MM, 460kg

RS Stock No: 621-9064



Product Details

RS Pro swivel castor ART36 has wheel diameter of 200 mm and load capacity of 460 kg. It features ball bearing hub for a strong and easy roll. This heavy duty caster has elastic rubber tyre for non-marking floor surface.



ENGLISH

Specifications:

Fixing Centres (Length)	105 mm
Fixing Centres (Width)	80 mm
Fixing Centres	105 x 80 mm
Fixing Hole Size	11 mm
Fixing Plate Dimensions	145 x 110 mm
Fixing Plate Length	145 mm
Fixing Plate Width	110 mm
Hub Bearing Type	Ball Bearing
Hub Material	Aluminium
Includes Brake	No
Load Capacity	460 kg
Number of Fixing Holes	4
Overall Height	235 mm
Rotation	Swivel
Tyre Material	Rubber
Weight Class	Heavy Duty
Wheel Diameter	200 mm
Wheel Width	50 mm