

ENGLISH

Datasheet

RS Pro Fixed Plate Castor ART36A 200MM, 460kg

RS Stock No: 621-9547



Product Details

RS Pro fixed castor wheel ART36A has diameter of 200 mm and load capacity of 460 kg. It features ball bearing hub for a strong and easy roll. This heavy duty caster has elastic rubber tyre for non-marking floor surface.



ENGLISH

Specifications:

Fixing Control (Longth)	105 mm
Fixing Centres (Length)	105 mm
Fixing Centres (Width)	80 mm
Fixing Centres	105 x 80 mm
Fixing Hole Size	11 mm
Fixing Plate Dimensions	145 x 110 mm
Fixing Plate Length	145 mm
Fixing Plate Width	110 mm
Hub Bearing Type	Ball Bearing
Hub Material	Aluminium
Includes Brake	No
Load Capacity	460 kg
Number of Fixing Holes	4
Overall Height	235 mm
Rotation	Fixed
Tyre Material	Rubber
Weight Class	Heavy Duty
Wheel Diameter	200 mm
Wheel Width	50 mm