

## Fixtures with LED



### VT-6076

#### HIGHLIGHTS :

WATTS



18

EQ. WATTS



100

LUMINOUS



1440

BEAM ANGLE



120

|                            |                    |
|----------------------------|--------------------|
| Item No                    | : VT-6076          |
| SKU Code                   | : 6282             |
| Watts                      | : 18               |
| EQ Watts                   | : 100              |
| Voltage                    | : AC:220-240V,50Hz |
| Lumen(lm)                  | : 1440             |
| Color Temperature          | : 6000K            |
| Beam Angle                 | : 120              |
| PF                         | : >0.5             |
| LED Chip Type              | : SMD              |
| CRI                        | : >70              |
| Energy rating label        | : A+               |
| Certification              | : CE,EMC,ROHS      |
| IP Rating Protection Class | : IP65             |
| Body type                  | : ABS+PC           |
| Dimmable                   | : No               |
| Life Time                  | : 20,000 Hours     |
| Operation Temperature      | : -25 ~50°C        |
| EAN code                   | : 3800157616461    |
| Unit size                  | : 600*86*70MM      |
| Packing details            | : 50               |
| Unit cbm                   | : 0                |

#### PRODUCT FEATURES

- Cost effective, safe retrof it for T8 Tubes
- Perfectly matches with the traditional daylight tube fixture
- Long Lifespan, Low maintenance and energy saving
- Available in 60 cm, 120 cm, 150 cm & 180 cm
- Widely used for Domestic and Commercial Lighting, Offices, Supermarkets, Shops, Hotels & similar environment

CLICK HERE  
FOR OTHER RELATED CERTIFICATES 