## HAND HELD CASES

## UNIVERSAL ENCLOSURES

HAND HELD CASES

HEAVY DUTY ENCLOSURES

DIN RAIL BOXES

INTERFACE SUPPORTS

CONTROL STATIONS

DIECAST & METAL BOXES

DESKTOP & INSTRUMENT CASES

POTTING BOXES

## EPDM rubber gasket

TYPE NO. CHH62GASK

IP65 protection

DESCRIPTION

31-IP Gasket

62-IP Gasket

*19"* • Operating temperature -20°C to +85°C *ENCLOSURES* 

19" SUBRACKS

CUSTOM SIZED ENCLOSURES

CUSTOM SERVICES


## 62 Series Pock Boxes


Contemporary range of small robust hand-held boxes with bevelled and rounded edges

- Moulded in high impact ABS, UL94-V0
- Snap-fit assembly
- · Recesses in lid and base for membrane keypads or overlays
- Excellent properties for machining
- Key-ring lug style available
- Optional EPDM gasket for IP65 seal

Material	Lid and base high impact ABS, UL94-V0		
Operating Temperature	Resistant to temperatures of up to 85°C		
Protection class	IP62 as standard		
	IP65 with gasket option		
Standard colours	Light grey similar to RAL 7035		
	Black similar to RAL 9004		
Standard unit includes	Lid & base		
Options	IP65 gasket		
	3 & 6 button membrane keypad		

BLACK	LIGHT GREY	LENGTH	WIDTH	HEIGHT	STYLE
CHH621BLK	CHH621GRY	55mm	40mm	18mm	-
CHH622BLK	CHH622GRY	60mm	40mm	18mm	key ring lug
CHH623BLK	CHH623GRY	70mm	50mm	20mm	-







Ver 1.0

