

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0643193211](#)
Status: **Active**
Overview: CMC and CMX Sealed, Hybrid, Modular Connectors
Description: .635mm, 1.50mm, CMC Receptacle, 32 Circuits, Right Wire Output, Black Coding, Mat Sealed

Documents:

3D Model	Application Specification AS-64319-002-SP-001 (PDF)
Drawing (PDF)	Application Specification AS-98420-002-001 (PDF)
Product Specification PS-64319-001-001 (PDF)	Application Specification AS-98420-002-CH-001 (PDF)
Product Specification PS-64319-002-001 (PDF)	Application Specification AS-98420-002-FR-001 (PDF)
Application Specification AS-64319-002-001 (PDF)	Application Specification AS-98420-002-SP-001 (PDF)
Application Specification AS-64319-002-CH-001 (PDF)	Packaging Specification PK-64319-001-001 (PDF)
Application Specification AS-64319-002-FR-001 (PDF)	RoHS Certificate of Compliance (PDF)

Application tooling part link

Application Tooling Part Link	63812-1100
Application Tooling Part Link	63824-1200

General

Product Family	Crimp Housings
Series	64319
Application	Automotive, Power, Wire-to-Board
Comments	Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C . Current max = 6.0A for 0.635mm Terminal (0.75mm ² wire) and 12.0A for 1.50mm Terminal (2.00mm ² wire), Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C . Current max = 6.0A for 0.635mm Terminal (0.75mm ² wire) and 12.0A for 1.50mm Terminal (2.00mm ² wire)

[More Detailed Tech Information](#)

Overview

Product Name	CMC and CMX Sealed, Hybrid, Modular Connectors
UPC	CMC 883906131135

Physical

Circuits (maximum)	32
Circuits Detail	8 x 1.5mm & 24 x 0.635mm terminals
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	29.426/g
Number of Rows	4
Packaging Type	Carton
Panel Mount	No



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[64319 Series](#)

Mates With

[643340100](#) 32-Circuit CMC header
[643330100](#) 112-Circuit CMC Header
[5022250801](#) 80-Circuit CMC Header

Use With

CMC CP Terminals [64322](#) , [64323](#). CMC Wire Cap [643191201](#). Sealing Plugs [643251010](#) , [643251023](#) , [643340100](#) , [643330100](#) , [5022250](#) 801

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Continuity Test Pen Assembly [638121100](#)

Pitch - Mating Interface 2.54mm, 3.70mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +125°C

Unlocking Tool [638241200](#)
for CMC and
CMX Receptacle
Connector

Electrical

Current - Maximum per Contact 12.0A, 6.0A

Solder Process Data

Lead-free Process Capability N/A

Material Info

Reference - Drawing Numbers

Application Specification AS-64319-002-001, AS-64319-002-CH-001,
AS-64319-002-FR-001, AS-64319-002-SP-001,
AS-98420-002-001, AS-98420-002-CH-001,
AS-98420-002-FR-001, AS-98420-002-SP-001
Packaging Specification PK-64319-001-001
Product Specification PS-64319-001-001, PS-64319-002-001
Sales Drawing SD-64319-001-001

This document was generated on 09/18/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION