

COAXIAL TERMINATION, 50 Ohm, SMB, plug (male)

65_SMB-50-0-31/133_N

Properties

- Various bandwidth
- Impedance matched
- Standard or precision types
- Low and medium power



Product configuration		
Interface	Gender	Standard
SMB	jack (female)	IEC 60169-10_MIL-STD-348A/311_CECC 22130

Electrical data	
Impedance	50Ω
Operating frequency	0 GHz ... 4 GHz
VSWR	1.35
Return loss	16.5 dB

Electrical Data (power)	
Average power	0.5 W at 25 °C ambient temperature. Linearly derated to 0.3 W at 65 °C ambient temperature.
Peak power	500 W peak power

Interface and material data		
Interface	SMB / jack (female)	
Piece parts	Material	Plating
Centre contact	Bronze	Gold Plating
Outer conductor	Brass	Tri-metal Plating
Body	Brass	Tri-metal Plating
Insulator	PFA / PTFE	
Piece parts	Material	Plating

Mechanical data	
Weight	0.006 kg

COAXIAL TERMINATION, 50 Ohm, SMB, plug (male)

65_SMB-50-0-31/133_N

Ordering Information Table	
Item number	Item description
85218401	65_SMB-50-0-31/133_NE

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P42149 / Date of publication: 28.11.2023 / uncontrolled copy