Completely pre-assembled Signal Towers / eSIGN

eSIGN 15 Segments with Siren



ļ

Part No.:	657.600.55		
Series:	eSIGN		
MECHAN	ICAL DATA		
Height		372 mm	
Diameter		72 mm	
Materials		PC	
Dome colour		Clear	
Housing colour		Black	
Protection category		IР66 IР69К	
Connection		M12 plug 8-pole	
Type of fixing		Base mounting Tube mounting	
Working temperature minimum		-30°C	
Working temperature maximum		+60°C	
Weight with packaging		840 g	
Product weight		780 g	
ELECTRICAL DATA			
Operating	g voltage	24V	
Operating voltage type		DC	
Operating voltage tolerance		+/- 10%	
Rated operational voltage		24 VDC	
Rated operational current		620 mA	
Rated inrush current		800 mA	
Protection class		Protection class 3	
Pollution degree		3	
Overvoltage category		I	
Request to external PSU		SELV/PELV	
connectivity		Digital entrance USB	
OPTICAL	DATA		
Light source		LED	
Light colour		MC >1.000.000 colours	
Optical signal image		Blink Double flash Flash Permanent Revolving Triple flash	
Service life optical		50,000 h maximum	

ACUSTICAL DATA

For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.

ļ

Completely pre-assembled Signal Towers / eSIGN

eSIGN 15 Segments with Siren

) (aluma a (mague) art 1 ma aliatara a a			
Volume (max) at 1m distance	105 dB		
Acoustic signal image	Multi-tone		
Number of tones	10 tone		
Acoustic service life	5,000 h minimum		
APPROVAL DATA			
Conforms with CE	Yes		
WEEE	Yes		
Conforms with RED directive	No		
Conforms with ATEX-directive	No		
Conforms with CCC-Ex	No		
Conforms with CCC	No		
Conforms with UL	No		
Conforms with FCC	No		
Conforms with IC	No		
EAC certificate available	No		
Conforms with UKCA (Importer)	Yes (WERMA (UK) Ltd.)		
Conforms with CMIM	No		
Conforms with AS-I	No		
Conforms with DNV	No		
Conforms with RoHS CN	No		
Conforms with VdS	No		

For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.