

Completely pre-assembled Signal Towers / eSIGN

eSIGN IO-Link 15 Segments with Siren



Part No.:	657.610.55	CC	RoHS2	.(II)	UK
Series:	eSIGN	()	КОП 3.2	t GL) us	CA

MECHANICAL DATA		
Height	372 mm	
Diameter	72 mm	
Materials	PC	
Dome colour	Clear	
Housing colour	Black	
Protection category	IP66 IP69K	
Connection	M12 plug 4-pole	
Type of fixing	Base mounting Tube mounting	
Working temperature minimum	-30°C	
Working temperature maximum	+60°C	
Weight with packaging	840 g	
Product weight	780 g	

ELECTRICAL DATA		
Operating voltage	24V	
Operating voltage type	DC	
Operating voltage tolerance	+/- 20%	
Rated operational voltage	24 VDC	
Rated operational current	620 mA	
Rated inrush current	800 mA	
Protection class	Protection class 3	
Pollution degree	3	
Overvoltage category	I	
Isolation voltage	Ui = 50V / Uimp = 330V	
Request to external PSU	SELV/PELV	
connectivity	IO-Link	

OPTICAL DATA		
Light source	LED	
Light colour	MC >1.000.000 colours	
Optical signal image	Blink Double flash Flash Permanent Revolving Triple flash	
Service life optical	50,000 h maximum	

ACUSTICAL DATA

For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.



Completely pre-assembled Signal Towers / eSIGN

eSIGN IO-Link 15 Segments with Siren

Volume (max) at 1m distance	105 dB (A)
Acoustic signal image	Multi-tone
Number of tones	10 tone
Volume adjustable	Software controlled
Volume adjustment range	80-105 dB (A)
Acoustic service life	5,000 h minimum

APPROVAL DATA		
Conforms with CE	Yes	
WEEE	Yes	
Conforms with RED directive	No	
Conforms with ATEX-directive	No	
Conforms with CCC-Ex	No	
Conforms with CCC	No	
Conforms with UL	cULus	
UL Type Rating	Type 4/4X/12/13	
Conforms with FCC	No	
Conforms with IC	No	
EAC certificate available	No	
Conforms with UKCA (Importer)	Yes (WERMA (UK) Ltd.)	
Conforms with CMIM	No	
Conforms with AS-I	No	
Conforms with DNV	No	
Conforms with RoHS CN	No	
Conforms with VdS	No	

For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.



Completely pre-assembled Signal Towers / eSIGN

eSIGN IO-Link 15 Segments with Siren

DRAWING Innerer Ring austrennbar für Rohrmontage/ Inner ring can be removed for tube mounting Ø72,5 342 Ø54 Ø72,5

For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.