

#### **FEATURES**

- Flexible can be wrapped around pipes
- Various lengths available
- Cut to length

# RS PRO 15W/m Trace Heating Cable Constant Wattage, Parallel Circuit, 240 V, 50m

RS Stock No.: 665-7419



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



#### **Product Description**

RS PRO range of parallel circuit heating tape, with a constant wattage output for process temperature maintenance applications. This tape is flexible enough to allow it to be spiralled around a suitable pipe or vessel. The heating tape consists of several short heating zones each connected across a pair of continuous bus-wire conductors.

Trace heating options include:

703-3108 - 15W/m, 110 V, 20m cable

703-3101 - 15W/m,110 V, 50m cable

703-3105 - 15W/m, 110 V, 100m cable

256-244 - 15W/m, 240 V, 20m cable

665-7419 - 15W/m, 240 V, 50m cable

665-7413 - 15W/m, 240 V, 100m cable

256-109 - Trace Heating Termination Kit

#### **General Specifications**

Cable Type	Constant Wattage; Parallel Circuit
Self-Regulating	No
Sheath Material	Silicone Rubber
Applications	Frost protection; Water, oil and chemical lines; Sprinkler system mains; Supply piping; Not for use in hazardous areas

#### **Electrical Specifications**

Output Per Metre	15W
Voltage Rating	240V

#### **Mechanical Specifications**

Length	50m
--------	-----



### **Operation Environment Specifications**

Operating Temperature Rating	-60 to 200°C
------------------------------	--------------



## Trace Heating Cable

