

## **FEATURES**

- High Grade Steel
- Two Layer Front Panel
- Powder Coated Enclosure
- Precise Design
- High Quality Manufacturing standard

# RS PRO Ventilated Rackmount Enclosure, 2U, 84 HP, Height 88.1mm, 245mm Deep

RS Stock No.: 665-7719



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## **Rackmount Enclosures**



#### **Product Description**

Introducing the RS PRO PF19 Rackmount Enclosures, a high quality and heavy-duty electronic enclosure series, suitable for a wide range of uses. Constructed from a mixture of high grade rolled steel and lightweight aluminium panels, these rackmount enclosures offer a sturdy construction and combined with the tough powder-coated finish, provide long-lasting life of the product even in harsh environments. The enclosures are easy to use and assemble, thanks to the precision workmanship and well-engineered design. In addition to this, the high-quality materials that are used to manufacture this RS PRO enclosure offer a strong and aesthetically-pleasing finished product, suitable for a wide range of applications both at home or in industry.

### **General Specifications**

Mounting	Rackmount
Rack Units	2U
Material	Steel
Horizontal Pitch	84HP
Ventilated	Yes
Handles	Yes
Colour	Black
For Use With	In outdoor conditions and exposure to the elements
Rack Size	Half Width
Features	The PF19 enclosure range is available in a wide variety of sizes
Sound Proof	No
Fan Included	No

#### **Mechanical Specifications**

Dimension	88.1 x 482.6 x 245mm
Height	88.1mm
Depth	245mm
Width	482.6mm



## Approvals

Declarations	RoHS Certificate of Compliance
Standards Met	IEC 297 / EIA RS-310 C1977 / DIN 41494 / ASTM D610-01 / ASTM B117

There are 24 different sizes and configurations which are available in :

- Height: 1.5U to 6U (B)

- Width: 482 (A) - Depth: 90, 245, 335, 425 and 465 (D)

