


Datasheet

Brass Pneumatic Quick Connect Coupling, G 1/8 Male, Threaded

RS Stock number 667-1807

021 [Quick Release Pneumatic Couplings]


Interchangeability

 RECTUS 2 RECTUS 90,
CAMOZZI

Temperature Range

-20 C +100 C (-4 F +212 F)

Working Pressure

0 - 35 bar (0 - 500 PSI)

Flow Capacity

NW - 5

Standard version

 Balls : Stainless Steel
Buna (N)

Options

F-Straight Through flow

K - Chrome Plated

N - Nickel Plated

T - NPTF Thread

V - Viton Seal

Material

Coupler Body : Brass Nickel Plated

Sleeve : Steel Body : Brass Nickel Plated

Valve : Brass


Springs : Stainless Steel

Locking O-Ring : Stainless Steel


Balls : Stainless Steel

Seals : Buna (N)






Plug : Brass Nickel Plated


Couplers and Plugs

Male Thread Coupler

Connection	Order No	SW	Length	Dia
g 1/8"	021 EG 10	14	36	16
G 1/4"	021 EG 13	17	38	16
G 3/8"	021 EG 17	19	38	16
M 12X1,5	021 EG 12	17	39	16
M 14X1,5	021 EG 14	17	39	16


Female Thread Coupler


G 1/8"	021 DG 10	14	36	16
G 1/4"	021 DG 13	17	38	16
G 3/8"	021 DG 17	19	38	16
M 12X1,5	021 DG 12	17	38	16
M 14X1,5	021 DG 14	17	38	16

 Standart Hose Barb Coupler	4mm 1/6"	021 HG 04	14	46	16
	6mm 1/4"	021 HG 06	14	46	16
	8mm 5/16"	021 HG 08	14	46	16
	9mm 5/14"	021 HG 09	14	46	16
	10mm 3/8"	021 HG 10	14	46	16
	6mm Parker 1/4"	021 HG 06 P	14	46	16
 Plastic Hose Coupler	4X6mm-M10X1	021 PG 04	14	41	16
	6X8mm-M10X1	021 PG 06	14	41	16
 Plastic Hose Coupler With Spring	4X6mm-M10X1	021 SG 04	14	53	16
	6X8mm-M12X1	021 SG 06	17	53	16
 Standart Hose Barb Plug	4mm-M10X1	021 MG 04	14	60	16
	5mm-M12X1	021 MG 05	14	60	16
	6mm-M12X1	021 MG 06	17	60	16
	6mm-M12X1	021 MG 08	17	60	16
 Plastic Hose Plug	4X6mm-M10X1	021 YG 04	14	125	16
	6X8mm-M10X1	021 YG 06	14	130	16




Male Thread Plug

4mm 1/6"	021 HU 04	32	9
5mm 1/5"	021 HU 05	32	9
6mm 1/4"	021 HU 06	32	9
8mm 5/16"	021 HU 08	32	9
9mm 5/14	021 HU 09	33	12
10mm 3/8"	021 HU 10	33	12
6mm Parker	021 HU 06 P	36	16




Female Thread Plug

4X6 mm- M10X1	021 PU 04	32	10
6X8 mm- M12X1	021 PU 06	32	12





Male Thread Plug

4X6mm- M10X1	021 SU 04	14	44
6X8mm- M12X1	021 SU 06	17	44



Male Thread Plug

4 mm- M10X1	021 MU 04	14	50
5 mm- M10X1	021 MU 05	14	50
6 mm- M12X1	021 MU 06	14	50
8 mm- M12X1	021 MU 08	14	50
9 mm- M12X1	021 MU 09	14	50
10 mm- M14X1	021 MU 10	17	50


Male Thread Plug
4X6mm-
021 YU 04
115
**M10X1
6X8 mm-
M10X1**
021 YU 06
120

Male Thread Plug
G1/8"
021 EU 10
14
25
G1/4"
021 EU 13
17
28
G3/8"
021 EU 17
19
28
M 10X1
021 EU 10 M
14
26
M 12X1,5
021 EU 12
17
28
M 14X1,5
021 EU 14
17
28

Male Thread Plug
G 1/8"
021 DU 10
14
25
G 1/4"
021 DU 13
17
26
G 3/8"
021 DU 17
19
27
M 10X1
021 DU 10 M
14
27
M 12X1,5
021 DU 12
17
27
M 14X1,5
021 DU 14
17
27