

Datasheet

ENGLISH

Brass Pneumatic Quick Connect Coupling, G 1/4 Female, Threaded

RS Stock number 6671838





Features

Interchangeability: Rectus 2, Rectus 90, Camozzi

Temp.Range: -20°C to +100°C

Working Pressure: 0-35 bar (0-500 PSI)

Flow Capacity: NW -5.5

Option: F - Straight- thru flow

T - NPTF Thread

K - Chrome plated

V - Viton Seal

Material

Coupler Body - Brass Nickel Plated

Sleeve - Steel Body: Brass Nickel Plated

Valve - Brass

Springs - Stainless Steel

Locking O-Ring Stainless Steel

Balls - Stainless Steel

Seals - Buna (N)

Plug - Brass Nickel Plated

Standard Version:

Balls: Stainless Steel

Buna (N)

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.