



Save as PDF



Peli protector cases - Total protection boxes - 1400 case



Interior dimensions:
30 x 22.5 x 13.2 cm (12" x 9" x 5")

Watertight, crushproof, and dust proof

- Easy-open, double-step latches
- Open cell core with solid wall design - strong, light weight
- O-ring seal
- Automatic Pressure Equalization Valve
- Stainless steel padlock protectors
- Comfortable, rubber over-moulded handle
- Stainless steel hardware
- Pick 'N' Pluck™ with convoluted lid foam
- Personalised nameplate service available
- Unconditionally Guaranteed



Black Silver Yellow Orange Desert_tan

Peli protector cases - Total protection boxes - 1400 case SPECIFICATIONS

Exterior Dimensions (L x W x D)			Interior Dimensions (L x W x D)		
33.9 x 29.5 x 15.2 cm (13" x 12" x 6")			30 x 22.5 x 13.2 cm (12" x 9" x 5")		
Lid Depth	Bottom Depth	Total Depth			
3 cm (1")	10.2 cm (4.00")	13.2 cm (5.18")			
Lid Depth	Bottom Depth	Total Depth			
3 cm (1.18")	10.2 cm (4.00")	13.2 cm (5.18")			
Weight w/Foam	Weight w/o Foam	Buoyancy Max.			
2 kg. (4.41 lbs)	1.8kg (3.97 lbs.)	9.1 kg (20.06 lbs.)			
Range Temperature					
-40 / 99° C (-40 / 210° F)					

Personalized Nameplate Available

1400 Case Certificates

- IP67(1 meter submersion for 30 minutes)
- MIL C-4150J
- Def Stan 81-41/STANAG 4280
- ATA 300

Materials

Body	Latch	Lid O-Ring	Pins
Polypropylene	ABS	PolymerStainless Steel	
Foam	Purge Body	Purge Vent	Purge O-Ring
1.3 lb Polyurethane	ABS	3 Micron Hydrophobic Non-Woven PET	70 Shore Nitrile

Configuration

Cat. #	Description
1400	Peli protector cases - Total protection boxes - 1400 case

Peli protector cases - Total protection boxes - 1400 case Accessories

Cat. #	Description