

Data Sheet

Bendable Double USB

Art. Nr. 67302100 (IV)

Art. Nr. 67302500 (EV)

07.11.2014

Input voltage:	8 - 34 Volt
Output voltage :	5 Volt
Output current max.:	5 A (2 x 2,5 A)
Input current duration:	4,4 A (2 x 2,2 A)
Current consumption:	< 5 mA (open circuit operation)
Overvoltage protection:	yes
Protection against overheating:	yes
Reverse voltage protection:	yes
Connectores:	cigarette lighter sockets and DIN standard sockets

Material:

Housing:	ABS
Temperature stress:	max. 110 °C
Connection spring::	Cu Sn 6
Surface:	bright pickled
Connection sleeve:	Cu Zn 37 F45
Surface:	gal. Ni 5
Plug pin:	Cu Zn 40 Pb 2
Surface:	gal. Ni 5

Bendable Double USB

Art. Nr. 67302100 (IV)

Art. Nr. 67302500 (EV)

07.11.2014

