

## Data Sheet

### **Built-In Socket including 1 power USB socket and 2 power socket**

Art. Nr. 67326000 (BP)

Art. Nr. 67326500 (SP)

06.04.2020

1 Power Double USB Socket

2 Power Socket 21 mm Ø

Input voltage: max. 24 V DC

Current load total: max. 20 A based on a cable cross  
section of 2.5 mm<sup>2</sup>

max. 16 A based on a cable cross  
section of 1.5 mm<sup>2</sup>

Connection: ca. 200mm cable

#### **Power Double USB Socket**

Output voltage : 5 V DC

Output current: 4.2 A total (duration)

5 A total (short time)

Current consumption: < 3 mA (idle)

Protection against: Overload, overtemperature,  
reverse voltage

#### **Material housing:**

Frame: Polycarbonate

Power socket: Polycarbonate / Metal

USB socket: ABS

Temperature stress: max.110° C

**Built-In Socket including 1 power USB socket  
and 2 power socket**

Art. Nr. 67326000 (BP)

Art. Nr. 67326500 (SP)

06.04.2020

