

Data Sheet

Built-In Socket including 1 power USB socket and 2 power socket

Art. Nr. 67346000 (BP)

Art. Nr. 67346500 (SP)

06.04.2020

1 Power Double USB C/A Socket

2 Power Socket 21 mm Ø

Input voltage: max. 24 V DC

Current load total: max. 20 A based on a cable cross
section of 2.5 mm²

max. 16 A based on a cable cross
section of 1.5 mm²

Connection: ca. 200mm cable

Power Double USB C/A Socket

Output voltage : 5 V DC

Output current: 3.6 A total

Current consumption: < 1 mA (idle)

Protection against: short circuit , overvoltage overload,
overtemperature, reverse voltage

Material housing:

Frame: Polycarbonate

Power socket: Polycarbonate / Metal

USB socket: ABS

Temperature stress: max.110° C

**Built-In Socket including 1 power USB socket
and 2 power socket**

Art. Nr. 67346000 (BP)
Art. Nr. 67346500 (SP)

06.04.2020

