

## Datasheet

# HSS 6 Piece 90° Three-Flute Countersink Set

RS Stock number [673-8697](#)



### Description:

90° flutes for use with machines and portable tools.

Three-flute designed to reduce clogging, improve clearance and be chatter free.

Three-flute for use on metals only.

Five-flute for use on metal and wood.

### Specifications:

Countersink Angle:	90°
Kit Contents:	6.3; 8.3; 10.4; 12.4; 16.5; 20.5 mm
Largest Head Diameter:	20.5 mm
Material:	HSS
Number of Flutes:	3
Number of Pieces:	6
Smallest Head Diameter:	6.3 mm

**90deg 3 flute countersinks, round shank**

RS STOCK NUMBER	MANUFACTURE PART NO.	NOMINAL HEAD DIA.	OVERALL LENGTH	SHANK LENGTH	SHANK DIA.	POINT ANGLE	NO. OF FLUTE	Old Stock No.
6738691	T51000633	6.3mm	45mm	35mm	5mm	90°	3	3643745
6738701	T51000833	8.3mm	50mm	38mm	6mm	90°	3	3643751
6738704	T51001043	10.4mm	50mm	36mm	6mm	90°	3	3643773
6738708	T51001243	12.4mm	56mm	41mm	8mm	90°	3	3643789
6738717	T51001653	16.5mm	60mm	42mm	10mm	90°	3	3643795
6738710	T51002053	20.5mm	63mm	42mm	10mm	90°	3	3643802
6738697	T9913	6.3,8.3,10.4,12.4,16.5,20.5mm in metal box					3	3643739