

Data Sheet

DIN Standard Built-In Socket

Item-No. 67607000 (Bulk Packaging)
Item-No. 67617000 (Individual Packaging)

07.02.2018

Tension range:	max. 24 Volt
Max. current load:	max. 16 Amp
Terminal:	6,3 mm T- flat connectors
Panel thickness:	2 - 9 mm
Mounting hole:	min. \varnothing 18 mm

Material Einbausteckdose:

Housing:	Polycarbonate
Stress of temperature:	max. 135 °C
Contact spring:	Cu Sn 6 HV 160
surface:	nickel
Contact sleeve:	Cu Zn 37 F45
surface:	nickel

DIN Standard Built-In Socket

Item-No. 67607000 (Bulk Packaging)
Item-No. 67617000 (Individual Packaging)

07.02.2018

