

Data Sheet

DIN Standard Built-In Socket with mounting plate

Item-No. 67607030(Bulk Packaging)
Item-No. 67617030 (Individual Packaging)

07.02.2018

Tension range:	max. 24 Volt
Max. Current load:	max. 16 Amp
Terminal:	6,3 mm T- flat connectors
Panel thickness:	any
Mounting hole:	min. ø25,4 mm

Material Einbausteckdose:

Housing:	Polycarbonat
Stress of temperature:	max. 135 °C
Mounting plate:	ABS
Contact spring:	Cu Sn 6 HV 160
surface:	nickel
Contact sleeve:	Cu Zn 37 F45
surface:	nickel

DIN Standard Built-In Socket with mounting plate

Item-No. 67607030 (Bulk Packaging)
Item-No. 67617030 (Individual Packaging)

07.02.2018

