

## Data Sheet

### DIN Standard Built-In Socket with protective cap

Item-No. 67607100 (Bulk Packaging)  
Item-No. 67617100 (Individual Packaging)

07.02.2018

|                    |                           |
|--------------------|---------------------------|
| Tension range:     | max. 24 Volt              |
| Max. current load: | max. 16 Amp               |
| Terminal:          | 6,3 mm T- flat connectors |
| Panel thickness:   | 2 - 9 mm                  |
| Mounting hole:     | min. $\varnothing$ 18 mm  |

#### **Material Einbausteckdose:**

|                        |                |
|------------------------|----------------|
| Housing:               | Polycarbonat   |
| Stress of temperature: | max. 135 °C    |
| Concat spring:         | Cu Sn 6 HV 160 |
| surface:               | nickel         |
| Contact sleeve:        | Cu Zn 37 F45   |
| surface:               | nickel         |
| Protection cap:        | Polycarbonat   |

## Data Sheet

### DIN Standard Built-In Socket with protective cap

Item-No. 67607100 (Bulk Packaging)  
Item-No. 67617100 (Individual Packaging)

09.02.2018

