

Data Sheet

DIN Standard Built-In Socket with protective cap & mounting plate

Item-No. 67607130 (Bulk Packaging)
Item-No. 67617130 (Individual Packaging)

07.02.2018

| | |
|--------------------|----------------------------|
| Tension range: | max. 24 Volt |
| Max. Current load: | max. 16 Amp |
| Terminal: | 6,3 mm T- flat connectors |
| Panel thickness: | any |
| Mounting hole: | min. \varnothing 25,4 mm |

Material Einbausteckdose:

| | |
|------------------------|----------------|
| Housing: | Polycarbonat |
| Stress of temperature: | max. 135 °C |
| Mounting plate: | ABS |
| Contact spring: | Cu Sn 6 HV 160 |
| surface: | nickel |
| Contact sleeve: | Cu Zn 37 F45 |
| surface: | nickel |
| protective cap | Polycarbonat |

**DIN Standard Built-In Socket with
protective cap & mounting plate**

Item-No. 67607130 (Bulk Packaging)
Item-No. 67617130 (Individual Packaging)

07.02.2018

