

FEATURES

- **Non-slip main handle and low friction**
- **Provides two-hand grip in the final phase of crimping**
- **Full cycle crimp mechanism to ensure consistent, reliable crimp**
- **Ratchet release mechanism to clear mis-crimps and obstructions**
- **Precision eccentric**
- **Each tool has a unique serial number for traceability**
- **Durable: life span exceeds 50000 cycles**
- **High strength, through hardened alloy Swedish steel construction**

RS PRO Plier Crimping Tool for BNC, TNC

RS Stock No.: 683-1627



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO crimping tool is an "Original line" hand crimp tool for BNC, TNC and N coaxial cable connectors. Producing 5.41 mm, 6.48 mm, 1.69 mm/.213",.255", 0.067" hexagon shaped crimps, with the minimum of effort, either right or left handed. Suitable for cable types RG108A/U, RG142B/U, RG210/U, RG223/U, RG302/U, RG58C/U, RG59B/U, RG62A/U, RG62B/U, RG71B/U

General Specifications

Crimp Tool Type	Plier
Crimp Connector Type	BNC, TNC
Crimp Profile	Hexagon
Applications	Maintenance & repair, Electrical Installations, Cable assemblies

Mechanical Specifications

Overall Length	198mm
Width	18 mm/0.71"
Height	59 mm/2.32"
Height Safe	Yes/No
Wire Size (mm²)	RG58, RG59, RG62, RG71
Life span, cycles	50000
Weight	350 g/0.77 lb
Crimp nest	5.41 mm/.213" 6.48 mm/.255" 1.69 mm/.067"

Approvals

Standards Met	RoHS Compliant
----------------------	----------------

