

69710-1 ✓ ACTIVE

AMP

TE Internal #: 69710-1

Portable Crimp Tools, Premium Crimp Tooling, Not Releasable,
Not Adjustable, Removable/Interchangeable, TE Product
Specification (114-)

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **TE Product Specification (114-)**

TE Certification: **Cannot be Certified**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Other
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Battery, Electric, Manual
Tooling Type	Straight Action Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM71-A17
POWERBAND CONTACTS



TE Part # 69735
PIDG STRATO 12-10 DIE SET



TE Part # 1-1377174-7
SMP 0-0165049-0



TE Part # 69734
PIDG STRATO 14 DIE SET



TE Part # 66262-2
MALE CONTACT ASSY. (L.P.)



TE Part # 66259-2
MALE CONTACT ASSY. (L.P.)



TE Part # 66740-8
TYPE XII FEMALE CONT (L.P.)



TE Part # 66261-1
MALE CONTACT ASSY. (L.P.)



TE Part # 66741-2
TYPE XII FEMALE CONT (L.P.)



TE Part # 66259-4
MALE CONTACT ASSY. (L.P.)




TE Part # 66261-4
MALE CONTACT ASSY. (L.P.)



TE Part # 66261-2
MALE CONTACT ASSY. (L.P.)



Customers Also Bought



Documents



Product Drawings

C-HEAD FRAME W/O DIES

English

Datasheets & Catalog Pages

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

AMP Circular Connectors for Commercial Signal & Power Applications Continued

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Agency Approvals

CSA Certificate

English