



LOGO! TD text display, 6-line, 3 background colors, 2 Ethernet ports, installation accessories for LOGO! 8

General information	
Product type designation	Text display
Suitability for use	Can be used with LOGO! 8 and higher
Display	
Design of display	FSTN
Line display	
<ul style="list-style-type: none"> Number of lines Number of characters per line 	6 20
Backlighting	
<ul style="list-style-type: none"> Type of backlighting 	LED
Control elements	
Keyboard fonts	
<ul style="list-style-type: none"> System keys <ul style="list-style-type: none"> Number of configurable system keys alphanumeric keyboard 	Yes 0 No
Installation type/mounting	
Wall mounting/direct mounting	No
Supply voltage	
Type of supply voltage	AC/DC
Rated value (DC)	12 V
Power loss	
Power loss, typ.	1.8 W; At 24 V DC
Interrupts/diagnostics/status information	
Diagnostics function	No
Standards, approvals, certificates	
CE mark	Yes
UL approval	Yes
FM approval	Yes
KC approval	Yes
Marine approval	
<ul style="list-style-type: none"> American Bureau of Shipping (ABS) 	Yes
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> min. max. 	-20 °C; No condensation 55 °C
Ambient temperature during storage/transportation	
<ul style="list-style-type: none"> min. 	-40 °C

• max.	70 °C
Altitude during operation relating to sea level	
• Ambient air temperature-barometric pressure-altitude	Tmin ... Tmax at 1 080 hPa ... 795 hPa (-1 000 m ... +2 000 m)
Configuration	
Configuration software	
• Configuration tool	LOGO! Soft Comfort V8
Mechanics/material	
Design of housing	plastic
Dimensions	
Width	128.2 mm
Height	86 mm
Depth	38.7 mm
Overall depth	38.7 mm
Weights	
Weight, approx.	220 g
Scope of supply	
Delivery quantity in pieces	1
last modified:	12/3/2020 