



SIMATIC DP, DP/DP coupler Coupling module for connecting of two PROFIBUS DP networks redundant current infeed

Figure similar

Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Input current	
Current consumption, typ.	90 mA
Power loss	
Power loss, typ.	2 W
Protocols	
PROFIBUS DP	Yes
AS-Interface	No
Interrupts/diagnostics/status information	
Status indicator	Yes
Diagnostics function	Yes
Degree and class of protection	
IP degree of protection	IP20
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	60 °C
Dimensions	
Width	40 mm
Height	127 mm
Depth	117 mm

last modified: 1/16/2021