



SIMATIC ET 200SP, BaseUnit BU15-P16+A10+2D, BU type A0, Pack quantity: 10 units, Push-in terminals, with 10 AUX terminals, New load group, WxH: 15 mmx141 mm

Figure similar

General information	
Product type designation	BU type A0
HW functional status	From FS07
Supply voltage	
Rated value (DC)	24 V
external protection for power supply lines	Yes; 24 V DC/10 A miniature circuit breaker with type B or C tripping characteristic
Current carrying capacity	
For P1 and P2 bus, max.	10 A
For AUX bus, max.	10 A
For process terminals, max.	2 A
Hardware configuration	
Formation of potential groups	
<ul style="list-style-type: none"> New potential group 	Yes
<ul style="list-style-type: none"> Potential group continued from the left 	No
Slots	
<ul style="list-style-type: none"> Number of slots 	1; Type A0
Potential separation	
between the potential groups	Yes
Isolation	
Isolation tested with	707 V DC (type test)
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> horizontal installation, min. 	-30 °C
<ul style="list-style-type: none"> horizontal installation, max. 	60 °C
<ul style="list-style-type: none"> vertical installation, min. 	-30 °C
<ul style="list-style-type: none"> vertical installation, max. 	50 °C
Altitude during operation relating to sea level	
<ul style="list-style-type: none"> Installation altitude above sea level, max. 	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
Accessories	
Color coding labels	
<ul style="list-style-type: none"> for process terminals 	CC00 to CC09
<ul style="list-style-type: none"> for AUX terminals 	CC71 to CC73
<ul style="list-style-type: none"> for add-on terminals 	does not exist
connection method / header	
Terminals	
<ul style="list-style-type: none"> Terminal type 	Push-in terminal
<ul style="list-style-type: none"> Conductor cross-section, min. 	0.14 mm ² ; AWG 26

• Conductor cross-section, max.	2.5 mm ² ; AWG 14
• Number of process terminals to I/O module	16
• Number of terminals to AUX bus	10
• Number of add-on terminals	0
• Number of terminals with connection to P1 and P2 bus	2

Dimensions

Width	15 mm
Height	141 mm
Depth	35 mm

Weights

Weight, approx.	50 g
-----------------	------

last modified: 1/16/2021 