SIEMENS

Data sheet

6ES7505-0RA00-0AB0



SIMATIC S7-1500, System power supply PS 60W 24/48/60 V DC, supplies the backplane bus of the S7-1500 with operating voltage

General information	
Product type designation	PS 60 W 24/48/60 V DC
HW functional status	FS03
Firmware version	V1.0.0
Engineering with	
STEP 7 TIA Portal configurable/integrated from	V12 / V12
version	
 STEP 7 configurable/integrated from version 	V5.5 SP3 or higher
Installation type/mounting	
Rail mounting	Yes
Supply voltage	
Rated value (DC)	24 V / 48 V / 60 V
permissible range, lower limit (DC)	19.2 V; Static 19.2 V, dynamic 18.5 V
permissible range, upper limit (DC)	72 V; Static 72 V, dynamic 75.5 V
Reverse polarity protection	Yes
Short-circuit protection	Yes
Mains buffering	
 Mains/voltage failure stored energy time 	20 ms
Input current	
Rated value at 24 V DC	3 A
Rated value at 48 V DC	1.5 A
Rated value at 60 V DC	1.2 A
Output current	
Short-circuit protection	Yes
Power	
Infeed power to the backplane bus	60 W
Power loss	
Power loss at nominal rating conditions	12 W
Interrupts/diagnostics/status information	
Status indicator	Yes
Potential separation	
primary/secondary	Yes; Electrical isolation for 230 V AC (reinforced isolation)
Isolation	, , , , , ,
Isolation tested with	2 500 V DC/2 s (routine test)
EMC	
Interference immunity against voltage surge	
Interference immunity of supply lines acc. to IEC 61000-4-5	Yes; ±1 kV (acc. to IEC 61000-4-5; 1995; surge symm.), ±2 kV (acc. to IEC 61000-4-5; 1995; surge asymm.), no external protective circuit required

Degree and class of protection	
IP20	
I, with protective conductor	
Dimensions	
70 mm	
147 mm	
129 mm	
600 g	

last modified:

9/8/2021 🖸