



Figure similar

SIMATIC S7-1500, digital input module DI 16x230 V AC BA, 16 channels in groups of 4; Input delay 20 ms; Input type 1 (IEC 61131); Front connector (screw terminals or push-in) to be ordered separately

General information	
Product type designation	DI 16x230VAC BA
HW functional status	FS01
Firmware version	V2.0.0
<ul style="list-style-type: none"> FW update possible 	Yes
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; I&M0 to I&M3
<ul style="list-style-type: none"> Isochronous mode 	No
<ul style="list-style-type: none"> Prioritized startup 	Yes
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated from version 	V12 / V12
<ul style="list-style-type: none"> STEP 7 configurable/integrated from version 	V5.5 SP3 / -
<ul style="list-style-type: none"> PROFIBUS from GSD version/GSD revision 	V1.0 / V5.1
<ul style="list-style-type: none"> PROFINET from GSD version/GSD revision 	V2.3 / -
Operating mode	
<ul style="list-style-type: none"> DI 	Yes
<ul style="list-style-type: none"> Counter 	No
<ul style="list-style-type: none"> MSI 	Yes
Power	
Power available from the backplane bus	1 W
Power loss	
Power loss, typ.	4.9 W
Digital inputs	
Number of digital inputs	16
Digital inputs, parameterizable	No
Source/sink input	P-reading
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Input voltage	
<ul style="list-style-type: none"> Rated value (AC) 	230 V; 120/230 V AC, 50/60 Hz
<ul style="list-style-type: none"> for signal "0" 	0V AC to 40V AC
<ul style="list-style-type: none"> for signal "1" 	79V AC to 264V AC
Input current	
<ul style="list-style-type: none"> for signal "1", typ. 	11 mA; At 230 V AC and 5.5 mA at 120 V AC
Input delay (for rated value of input voltage)	
for standard inputs	
<ul style="list-style-type: none"> parameterizable 	No
<ul style="list-style-type: none"> at "0" to "1", max. 	25 ms

— at "1" to "0", max.	25 ms
for interrupt inputs	
— parameterizable	No
for technological functions	
— parameterizable	No
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
— permissible quiescent current (2-wire sensor), max.	2 mA
Interrupts/diagnostics/status information	
Diagnostics function	No
Alarms	
• Diagnostic alarm	No
• Hardware interrupt	No
Diagnoses	
• Monitoring the supply voltage	No
• Wire-break	No
• Short-circuit	No
Diagnostics indication LED	
• RUN LED	Yes; green LED
• ERROR LED	Yes; red LED
• Monitoring of the supply voltage (PWR-LED)	No
• Channel status display	Yes; green LED
• for channel diagnostics	No
• for module diagnostics	Yes; red LED
Potential separation	
Potential separation channels	
• between the channels	No
• between the channels, in groups of	4
• between the channels and backplane bus	Yes
Permissible potential difference	
between different circuits	250 V AC between the channels and the backplane bus; 500 V AC between the channels
Isolation	
Isolation tested with	3 100 V DC
Standards, approvals, certificates	
Suitable for safety functions	No
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	0 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	0 °C
• vertical installation, max.	40 °C
Dimensions	
Width	35 mm
Height	147 mm
Depth	129 mm
Weights	
Weight, approx.	300 g
last modified:	1/19/2021 